

Notice technique noir de contrôle



ColorMatic Quick Check spray for checking sanded surfaces to identify irregularities. Produces a temporary gloss which evaporates residue-free. Also useable for the checking the color of spray samples.

Application:

The ideal assistant for perfect sanding following clear coat application.

Quality and properties

- Sprays gloss in a matter of seconds
- Evaporates residue-free
- Useful for identifying smallest dents and irregularities
- Produces colorfast spray samples
- Easy to use
- Ensures perfect results

Physical and chemical data

- **Basis of binder:** Aliphatic hydrocarbons
- **Colour:** transparent
- **Smell:** solvent
- **Substrate:**
sanded primer or filler areas
- **Storage stability:**
10 years if appropriate storage provided (=10°-25°C, relative air humidity of max. 60%)
- **Size:**
Aerosol cans, maximum nominal volume 400 ml
- **VOC-value:** 276,0g

Environnement et réglementation

Respect de l'environnement : Les produits European Aerosols sont 100% exempts de métaux lourds et utilisent des propulseurs garantis sans HCFC depuis 1977. Les capuchons et les emballages sont issus de matériaux recyclés.

Traitement des déchets : Seuls les aérosols vides doivent être portés au recyclage. Les contenants non vides doivent être apportés dans un centre de collecte spécifique.

Etiquetage réglementaire : Tous les produits European Aerosols respectent les dispositions en matière d'étiquetage prévues par la Directive 1999/45/EG. Tous les aérosols correspondent au TRGS 200 et TRG 300 ainsi qu'à la Directive 75/324/EWG dans sa variation actuelle.



- No special preparation required before applying ColorMatic Quick Check spray
- Shake the can for 5 seconds
- Surface check: Apply ColorMatic Quick Check in 1-2 thin layers. Rub with a paper tissue until an even surface film is arising
- Color check: Apply ColorMatic Quick Check on the basecoat lacquered spray sample and also on the car part which is for comparison
- After 20 minutes (depends on ambient temperature) the film is residue-free evaporated
- Tolerability testing is needed
- **For professional use only**
- **Wear an appropriate respirator (recommended type A2/P3)**



5 sec



1-2



Non-responsabilité

La présente fiche technique informe sans engagement sur les caractéristiques du produit suivant le niveau actuel de la technique. Nos consignes de mise en œuvre doivent être ajustées en fonction des conditions locales et des matières et appareils utilisés. Veuillez également observer les droits de protection industrielle applicables. Tous droits réservés.

Version : 8 juillet 2010

Cette version annule toutes les versions publiées antérieurement.

Date d'impression: 28.04.2024

European Aerosols GmbH | Kurt-Vogelsang-Straße 6 | 74855 Haßmersheim | info-de@european-aerosols.com

1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 31 32 33 34 35 36 37 38 39 40 41 42 43 44 45 46 47 48 49 50 51 52 53 54 55 56 57 58 59 60 61 62 63 64 65 66 67 68 69 70 71 72 73 74 75 76 77 78 79 80 81 82 83 84 85 86 87 88 89 90 91 92 93 94 95 96 97 98 99 100